



PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	NRN 47129	10/22	SEE PDM



MATERIAL:	
BODY & CONTACT:	BERYLLIUM COPPER ALLOY C17300 PER ASTM B196
INSULATOR:	PTFE PER ASTM D1710, TYPE I, GRADE 1, CLASS B
FINISH:	
BODY & CONTACT:	GOLD PER ASTM B 488, TYPE I, CODE C, CLASS 0.51; OVER COPPER PER AMS-2418, TYPE 1, .00005" MIN.
PERFORMANCE:	
IMPEDANCE:	50 OHMS
FREQ. RANGE:	DC TO 65.0 GHz
VSWR:	1.30:1 DC TO 65.0 GHz

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: $\pm 1/64$ ANGULAR: X° $\pm 1^{\circ}0'$
-----------	-----------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[1132-4139](#)