

LRU SERIES FUSE REDUCERS



Description

Littelfuse® fuse reducers allow smaller size fuses to be installed into existing fuse clips to prevent overfusing.

Features/Benefits

- Simple installation
- Reduces inventory requirements
- Silver brazed joints for maximum strength
- UL Listed (File No. E136855)
- CSA Certified (File No. LR92899)

Web Resources

Downloadable CAD drawings, FAQs, and other technical information visit: Littelfuse.com/lruh

Littelfuse.com/lrur

Littelfuse.com/lruj

Ordering Information

250 Volt

CATALOG/ORDERING NUMBER		FUSE CLIP	FUSE CASE SIZE
CLASS H/K5	CLASS R		
LRU 263	LRU 263 R	60 A	30 A
LRU 213	LRU 213 R	100 A	30 A
LRU 216	LRU 216 R	100 A	60 A
LRU 226	LRU 226 R	200 A	60 A
LRU 2621	LRU 2621 R	200 A	100 A
LRU 2641	LRU 2641 R	400 A	100 A
LRU 2642	LRU 2642 R	400 A	200 A
LRU 2661	LRU 2661 R	600 A	100 A
LRU 2662	LRU 2662 R	600 A	200 A
LRU 2664	LRU 2664 R*	600 A	400 A

*Only one reducer required.

600 Volt

CATALOG /ORDERING NUMBER			FUSE CLIP	FUSE CASE SIZE
CLASS H/K5	CLASS R	CLASS J		
LRU 663	LRU 663 R	LRUJ63	60 A	30 A
LRU 216	LRU 216 R	LRUJ13	100 A	30 A
LRU 616	LRU 616 R	LRUJ16†	100 A	60 A
LRU 626	LRU 626 R	LRUJ26	200 A	60 A
LRU 2621	LRU 2621 R	LRUJ21	200 A	100 A
LRU 2641	LRU 2641 R	LRUJ41	400 A	100 A
LRU 2642	LRU 2642 R	LRUJ42	400 A	200 A
LRU 2661	LRU 2661 R	—	600 A	100 A
LRU 2662	LRU 2662 R	—	600 A	200 A
LRU 2664	LRU 2664 R†	LRUJ64	600 A	400 A

†Only one reducer required.

†Fuse and reducer combination is slightly larger in diameter than 100 A Class J fuses. For specific applications, contact factory.

Class J reducers cannot be used in bolt-on applications.

Recommended Fuses

Class H/K5 Fuse Reducers

NLN / NLS

RLN / RLS

Class R Fuse Reducers

FLNR / FLSR

FLNR_ID / FLSR_ID

IDSR

LLNRK / LLSRK

LLSRK_ID

KLNR / KLSR

Class J Fuse Reducers

JTD_ID / JTD

JLS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[LRU616](#) [LRU216](#) [LRU226](#) [LRUJ13](#) [LRUJ16](#) [LRUJ41](#) [LRUJ42](#) [LRUJ63](#) [LRUJ64](#) [LRUJ21](#) [LRUJ26](#) [LRU226R](#)
[LRU2641](#) [LRU2642](#) [LRU2664](#) [LRU2662](#) [LRU2661](#) [LRU2621](#) [LRU216R](#) [LRU213R](#) [LRU213M](#) [LRU626](#) [LRU663M](#)
[LRU663R](#) [LRU2662R](#) [LRU2664R](#) [LRU626R](#) [LRU2661R](#) [LRU2642R](#) [LRU2641R](#) [LRU616R](#) [LRU263R](#) [LRU263M](#)
[LRU2621R](#) [LRU263](#) [LRU213](#) [LRU663](#)