



NC3FAH2-DA

3 pole female XLR receptacle, grounding: mating connector shell to pin1 and front panel, horizontal PCB mount, asymmetric push

The `State of the Art` receptacle. Round plastic body XLR PCB mount panel connector. These have the smallest size and highest packing density (23mm between centres). With the asymmetric push an additional space saving of appr. 20 % can be achieved. New designed tulip type contacts with hard gold plating and polished contact areas. UL recognized component.

Features & Benefits

- ✓ Smallest XLR receptacles, highest packing density
- ✓ Plastic housing, steel latch lock
- ✓ Tulip type female contact
- ✓ Polished contact areas and hard gold plating
- ✓ Housing flammability UL94 V-0
- ✓ For space sensitive applications - 20 % space saving

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[NC3FAH2-LR-DAE](#)