



Maximize Productivity with the High Performance HCT-910 Hot Air Rework System

The Metcal HCT-910 Hot Air Rework System offers a versatile solution for a wide variety of production and rework applications.

Features

- Versatile 900 W fast-heating hot air tool for soldering and desoldering applications
- Max temperature of 600 °C (1112 °F)
- Max airflow up to 120 l/m (4.2 cfm)
- Digital controls for both airflow & temperature, for increased precision
- On-the-fly manual mode – quickly toggle between temperature and flowrate
- Handpiece start/stop button & status light
- Tool-less nozzle removal & replacement
- ESD compliant
- TUV certified, CE listed

TECHNICAL SPECIFICATIONS

	HCT-910-11	HCT-910-21
Input Voltage (V)	115 V / 60 Hz	230 V / 50 Hz
Power	900 W	
Temperature Range	50 - 600 °C (122 - 1112 °F)	
Temperature Accuracy	3 30 °C (54 °F)	
Air Flow	At 300 °C, 5 - 120 l/m (0.2 - 4.2 cfm)	
Air Pump Type	Blower	
Hose Length (Panel-Handpiece)	1.2 m (3.9 ft)	
Noise	< 46 dB (A)	
Weight	2 kg (4.4 lbs)	
Safety Class	1	
Pollution Degree Category	II	
Storage Temperature	0 - 60 °C (32 - 140 °F)	
Surface Resistivity	Unit: 10 ⁵ Ω - 10 ⁶ Ω. Handpiece & Tube: 10 ⁷ Ω - 10 ¹¹ Ω	
Dimensions	21 x 14 x 14 cm (8.3 x 5.5 x 5.5 in)	
Certification/Approvals	cTUVus, CE, RoHS	

SYSTEMS SHIP WITH

HCT-910 Base Unit
5.0 mm Ø Bayonet Nozzle
Hand-piece Cradle
Power Cord

ACCESSORIES (sold separately)

HCT-910-HE-11	HCT-910 Replacement Heater, 115 V Input
HCT-910-HE-21	HCT-910 Replacement Heater, 230 V Input
HB-D25	HCT-910 Nozzle, Bayonet, 2.5 mm Ø
HB-D50	HCT-910 Nozzle, Bayonet, 5.0 mm Ø
HB-D100	HCT-910 Nozzle, Bayonet, 10.0 mm Ø
HB-D25-B	HCT-910 Bent Nozzle, Bayonet, 2.5 mm Ø
HB-D50-B	HCT-910 Bent Nozzle, Bayonet, 5.0 mm Ø
HB-ST	HCT-910 Nozzle, Bayonet, Shrink Tube
AC-PC1	HCT-910 Replacement Power Cord. 6 ft. (1.8 meters) 115 V

HCT-910 Nozzles are compatible with legacy HCT-900 and HCT- 1000 series systems. Visit Metcal.com for the full offering of nozzles.

For Sales and Support:

Metcal Corporate Headquarters
10800 Valley View Street,
Cypress, California, 90630, USA
Tel: 1-714-799-9910
Fax: 1-714-828-2001
E-mail:
orders@okinternational.com

Visit our website for more information and to
contact the Metcal office nearest you.

metcal.com/contact-us



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Metcal:

[HCT-910-11](#) [HCT-910-HE-11](#) [HCT-910-21](#)