



AMPMODU MOD. IV, IV.v, V Wire-to-Board .100" Centerline PRODUCT MATRIX

WIRE AWG	PRODUCT FAMILY
#20, #22 - #26, #28 - #32	MOD. IV, IV.v, V

PLATINGS	PRODUCT FAMILY
15μ" Gold	MOD. IV, IV.v, Short Point
30μ" Gold	MOD. IV, IV.v, V, Short Point
Tin	MOD. IV, IV.v, V, Short Point

RECOMMENDED POST LENGTHS	PRODUCT FAMILY
.185 - .283	MOD. IV, IV.v, V
.169 - .259	Short Point

APPLICATION TOOLING DESCRIPTION	APPLICATION TOOLING	
	PRODUCT FAMILY	
	MOD. IV, IV.v, V	SHORT POINT
Manual Hand Tool	●	●
AMP-O-MATIC Stripper/Crimper Machines with Applicator	●	●
Pneumatic Hand Tools		
AMP-O-LECTRIC Machines with Applicator	●	●
Tube-Fed-Discrete		
Tube-Fed Ribbon Cable Machine		
AMPOMATOR CLS Machines	●	●

te.com

© 2011 Tyco Electronics Corporation, a TE Connectivity Ltd. company. All Rights Reserved.

1773455-3 CIS WR 10/2011

AMPMODU, AMP-O-LECTRIC, AMP-O-MATIC, AMPOMATOR, TE Connectivity and the TE Connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

